

Halogen (75-130 V) Single End





Druh použití


- Stage & Theatre
- not relevant
- Professional Photography
- Club & Disco

Vlastnosti produktu

- Robust construction for reliable, lasting performance
- Consistent color over the life of the lamps
- Instant on and nearly constant luminous flux over the life of the lamp
- Broad product portfolio supporting the stage and studio markets
- Dimmable with traditional amber shift



Technický list řady výrobků



HALOGEN STUDIO LAMP 93734



HALOGEN STUDIO LAMP 64777, 64787, 64796



HALOGEN STUDIO LAMP 64805

Technický list řady výrobků

Technické údaje

Popis výrobku	Informace o produktu		Parametry	Physical Attributes & Dimensions
	Kód ANSI	LIF	Jmenovité napětí	Patice
64501 150 W 120 V	-	-	120 V	GX6.35
64514 300 W 120 V ¹⁾	-	CP/96	120 V	GX6.35
64512 300 W 120 V ¹⁾	FNS	-	120 V	GX6.35
PAR36 DWE MFL	DWE	-	120 V	screw terminal
64743 1000 W 120 V	FEL	CP/77	120 V	G9.5
93723 1200 W 80 V	-	CP/110	80 V	G22
64805 5000 W 120 V	DPY	-	120 V	G38/50

Popis výrobku	Životnost
	Average Rated Life
64501 150 W 120 V	50 hr
64514 300 W 120 V ¹⁾	75 hr
64512 300 W 120 V ¹⁾	15 hr
PAR36 DWE MFL	100 hr
64743 1000 W 120 V	300 hr
93723 1200 W 80 V	250 hr
64805 5000 W 120 V	500 hr

¹⁾ S technologií quartz pinch

Technický list řady výrobků

Bezpečnostní pokyny

Aby se zabránilo zranění osob nebo poškození majetku, halogenové výbojky smí být použity pouze ve vhodných svítidlech s vhodnými mechanismy (ochranné kryty, mřížky, atd.), aby se zajistilo, že v případě prasknutí výbojky neuniknou žádné díly/střepy a že během provozu neunikne ultrafialové záření. Kromě toho je nutné varovným piktogramem oznámit, že světelné zdroje vydávají vysoké úrovně tepla. Podrobné informace jsou k dispozici na vyžádání.

Pokyny k použití

Podrobnější informace k použití a grafiku najdete v technickém listu.

Vyloučení odpovědnosti

Změny bez předchozího upozornění vyhrazeny. Chyby a opomenutí vyhrazeny. Vždy se ujistěte, že používáte nejnovější vydání.