

Halogen (75-130 V) Single End





Druh použití


- Stage & Theatre
- not relevant
- Professional Photography
- Club & Disco

Vlastnosti produktu

- Robust construction for reliable, lasting performance
- Consistent color over the life of the lamps
- Instant on and nearly constant luminous flux over the life of the lamp
- Broad product portfolio supporting the stage and studio markets
- Dimmable with traditional amber shift



Technický list řady výrobků



HALOGEN STUDIO LAMP 93734



HALOGEN STUDIO LAMP 64777, 64787, 64796



HALOGEN STUDIO LAMP 64805

Technický list řady výrobků

Technické údaje

	Informace o produktu		Parametry	Physical Attributes & Dimensions
Popis výrobku	Kód ANSI	LIF	Jmenovité napětí	Patice
64501 150 W 120 V	-	-	120 V	GX6.35
64514 300 W 120 V ¹⁾	-	CP/96	120 V	GX6.35
64512 300 W 120 V ¹⁾	FNS	-	120 V	GX6.35
PAR36 DWE MFL	DWE	-	120 V	screw terminal
64743 1000 W 120 V	FEL	CP/77	120 V	G9.5
93723 1200 W 80 V	-	CP/110	80 V	G22
64805 5000 W 120 V	DPY	-	120 V	G38/50

	Životnost
Popis výrobku	Average Rated Life
64501 150 W 120 V	50 hr
64514 300 W 120 V ¹⁾	75 hr
64512 300 W 120 V ¹⁾	15 hr
PAR36 DWE MFL	100 hr
64743 1000 W 120 V	300 hr
93723 1200 W 80 V	250 hr
64805 5000 W 120 V	500 hr

¹⁾ S technologií quartz pinch

Technický list řady výrobků

Bezpečnostní pokyny

Aby se zabránilo zranění osob nebo poškození majetku, halogenové výbojky smí být použity pouze ve vhodných svítidlech s vhodnými mechanismy (ochranné kryty, mřížky, atd.), aby se zajistilo, že v případě prasknutí výbojky neuniknou žádné díly/střepy a že během provozu neunikne ultrafialové záření. Kromě toho je nutné varovným piktogramem oznámit, že světelné zdroje vydávají vysoké úrovně tepla. Podrobné informace jsou k dispozici na vyžádání.

Pokyny k použití

Podrobnější informace k použití a grafiku najdete v technickém listu.

Vyloučení odpovědnosti

Změny bez předchozího upozornění vyhrazeny. Chyby a opomenutí vyhrazeny. Vždy se ujistěte, že používáte nejnovější vydání.