

HBO Microlithography Lamps for Canon i-line Systems

Areas of application

- Microlithography



Product features and benefits

- High spectral intensity with peak irradiance at 365nm wavelength, making it ideal for microlithography
- Designed for long lasting performance
- Qualified with Canon
- Qualified with Canon



Product family datasheet

Technical data

Product description	Electrical Data		Photometric Data	Physical Attributes & Dimensions
	Nominal wattage	Nominal voltage	Light center length (LCL)	Length
HBO 1002 W/CEL	750 W	47 V	78.5 mm ²⁾	175.0 mm
HBO 1500 W/CIEL	1500 W	23.0 V	122.0 mm ²⁾	262.0 mm
HBO 2001 W/CIEL	2000 W	26 V	148.75 mm ²⁾	327.0 mm
HBO 2002 W/MA	2000 W	37 V	138.5 mm ²⁾	270.0 mm
HBO 2001 W/CIELX	2000 W	24.5 V		307.0 mm
HBO 2001 W/CIL	2000 W	26 V		309.0 mm
HBO 2700 W/CIL ¹⁾	2700 W	26 V	149.1 mm ²⁾	332.0 mm
HBO 4500 W/CIL ¹⁾	4500 W	30 V	157.75 mm ²⁾	354.0 mm

¹⁾ Lamp contains overpressure even in cold status - additional safety regulations, supplied with the lamps, have to be fulfilled. Please read Technical bulletin DO-SEM TB 004 carefully

²⁾ Distance from end of base to tip of anode or cathode (cold)

Product family datasheet

Safety advice

Because of their high luminance, UV radiation and high internal pressure (when hot) HBO lamps may only be operated in enclosed lamp casings specially constructed for the purpose. Mercury is released if the lamp breaks. Special safety precautions must be taken. More information is available on request or can be found in the leaflet included with the lamp or in the operating instructions.

Application advice

For more detailed application information and graphics please see product datasheet.

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.