

XBO Traditional & Xtreme Life (XL) Lamps




应用领域

- Film Projection
- Spotlights
- Searchlights
- Solar Simulation

产品特点


- High luminance (point source)
- Color temperature approximately 6000K - simulates daylight
- Continuous spectrum in the visible range
- High color rendering > 95
- High arc stability
- DC operation
- Hot restart
- Long lamp life with eXtreme Life technology
- Spectrum suitable for solar simulation applications



产品系列数据表



XBO XENON SHORT ARC LAMP - 3000WHTP CL



XBO XENON SHORT ARC LAMP - 2000 WH XL



XBO XENON SHORT ARC LAMPS

产品系列数据表

技术参数

产品描述	电参数		寿命
	标称功率	电流控制范围	Warranty hours
XBO 1000 W/HS OFR ¹⁾	1000 W	30...55 A	2000 hrs
XBO 1000 W/HSC OFR ²⁾	1000 W	30...55 A	2000 hrs
XBO 1000 W/HTP OFR ³⁾	1000 W	30...55 A	2400 hrs
XBO 2000 W/HS OFR ⁴⁾	2000 W	50...85 A	2400 hrs
XBO 1600 W XL OFR	1600 W	45...75 A	3500 hrs
XBO 1600 W/HSC XL OFR	1600 W	50...70 A	2500 hrs
XBO 2000 W/SHSC OFR ⁵⁾	2000 W	50...85 A	2000 hrs
XBO 2000 W/H XL OFR	2000 W	50...85 A	3500 hrs
XBO 2000 W/HTP XL OFR	2000 W	50...85 A	3500 hrs
XBO 2500 W/HS XL OFR	2500 W	70...100 A	2200 hrs
XBO 3000 W/H XL OFR	3000 W	70...110 A	2200 hrs
XBO 3000 W/HS XL OFR	3000 W	70...110 A	2200 hrs
XBO 3000 W/HTP XL OFR	3000 W	70...110 A	2200 hrs
XBO	3600 W		
XBO 4000 W/HSA OFR	4000 W	80...150 A	1000 hrs
XBO 4000 W/HS XL OFR	4000 W	80...150 A	1500 hrs
XBO 4000 W/HTP XL OFR	4000 W	100...140 A	1500 hrs
XBO 4500 W/HS XL OFR	4500 W	80...150 A	1400 hrs
XBO 4500 W/HTP XL OFR	4500 W	80...150 A	1400 hrs
XBO 5000 W/H XL OFR	5000 W	100...150 A	1200 hrs
XBO 5000 W/HBM XL OFR	5000 W	100...150 A	
XBO 6000 W/HS XL OFR	6000 W	110...165 A	750 hrs
XBO 6000 W/HTP XL OFR	6000 W	110...165 A	750 hrs
XBO 7000 W/HS XL OFR	7000 W	110...165 A	650 hrs
XBO 10000 W/HS OFR ¹⁾	10000 W	160...200 A	500 hrs

1) OFR = 无臭氧型号/H = 合适的水平燃烧位置/S = 短

2) OFR = 无臭氧型号/H = 合适的水平燃烧位置/S = 短/C = 带接线灯头

3) OFR = 无臭氧型号/H = 合适的水平燃烧位置/TM=螺纹针电缆

4) H = 合适的水平燃烧位置/S = 短

5) OFR = 无臭氧型号SHSC = 为水平燃烧的位置、阳极连接通过有线(超短)的额外短版本相似尺寸XBO 1600 A/HSC OFR

产品系列数据表

安全建议

Because of their high luminance, UV radiation and internal pressure in both the hot and cold state, XBO lamps may only be operated in enclosed lamp casings specially constructed for the purpose. Xenon lamps are highly explosive. When hot, xenon lamps can cause burn marks. They should only be handled when the lamp is at room temperature. Always use the protective jackets supplied when handling these lamps. When packing the lamps and when installing or removing the lamps without their protective jackets, always wear protective clothing (face shield with neck protector, protective jacket and lint-free, cut-resistant gloves). For more information see the relevant in-pack leaflets and operating instructions.

应用建议

更多详细应用信息和图形,请参阅产品数据表。

免责声明

更改恕不另行通知。遗漏错误不承担任何责任。总是确保使用最新的信息。