


TEC FLEX Low & High Power Protect

LED modules for semi-professional applications



Product family features

- Flexible and cuttable LED strip
- Luminous flux: up to 2,000 lm/m
- Available with color temperature: 2,700K, 3,000 K, 4,000 K
- Up to 50,000 hrs lifetime @ tc max
- Color consistency in 3 SDCM

Product family benefits

- Pre-wired LED strip, simple and quick plug-and-play installation
- Easy mounting on many smooth surfaces thanks to self-adhesive tape at the back
- Type of protection: IP66
- Dimmable (with suitable PWM dimming methods)



Technical data

Electrical data

Product description	Nominal voltage	Type of current	Rated wattage	Input voltage range	Accidental reverse input voltage protection up to
TFP300-G1 -827-05	24.0 V	DC	14.00 W	23...25 V	25 V
TFP300-G1 -830-05	24.0 V	DC	14.00 W	23...25 V	25 V
TFP300-G1 -840-05	24.0 V	DC	14.00 W	23...25 V	25 V
TFP300-G1 -865-05	24.0 V	DC	14.00 W	23...25 V	25 V
TFP300-G1 -850-05	24.0 V	DC	14.00 W	23...25 V	25 V
TFP1000-G1 -827-05	24.0 V	DC	47.50 W	23...25 V	25 V
TFP1000-G1 -830-05	24.0 V	DC	47.50 W	23...25 V	25 V
TFP1000-G1 -840-05	24.0 V	DC	47.50 W	23...25 V	25 V
TFP1000-G1 -865-05	24.0 V	DC	47.50 W	23...25 V	25 V
TFP1000-G1 -850-05	24.0 V	DC	47.50 W	23...25 V	25 V
TFP2000-G1 -827-05	24.0 V	DC	77.50 W	23...25 V	25 V
TFP2000-G1 -830-05	24.0 V	DC	77.50 W	23...25 V	25 V
TFP2000-G1 -840-05	24.0 V	DC	77.50 W	23...25 V	25 V
TFP2000-G1 -865-05	24.0 V	DC	77.50 W	23...25 V	25 V
TFP2000-G1 -850-05	24.0 V	DC	77.50 W	23...25 V	25 V

Photometrical data

Product description	Light color LED	Color rendering index Ra	Light color (designation)
TFP300-G1 -827-05	White	80	White
TFP300-G1 -830-05	White	80	White
TFP300-G1 -840-05	White	80	White
TFP300-G1 -865-05	White	80	White
TFP300-G1 -850-05	White	80	White
TFP1000-G1 -827-05	White	80	White
TFP1000-G1 -830-05	White	80	White
TFP1000-G1 -840-05	White	80	White
TFP1000-G1 -865-05	White	80	White
TFP1000-G1 -850-05	White	80	White
TFP2000-G1 -827-05	White	80	White
TFP2000-G1 -830-05	White	80	White
TFP2000-G1 -840-05	White	80	White
TFP2000-G1 -865-05	White	80	White
TFP2000-G1 -850-05	White	80	White

Dimensions & weight

Product description	Length	Product weight
TFP300-G1 -827-05	5000 mm	269.00 g
TFP300-G1 -830-05	5000 mm	269.00 g
TFP300-G1 -840-05	5000 mm	269.00 g
TFP300-G1 -865-05	5000 mm	269.00 g
TFP300-G1 -850-05	5000 mm	269.00 g
TFP1000-G1 -827-05	5000 mm	269.00 g
TFP1000-G1 -830-05	5000 mm	269.00 g
TFP1000-G1 -840-05	5000 mm	269.00 g
TFP1000-G1 -865-05	5000 mm	269.00 g
TFP1000-G1 -850-05	5000 mm	269.00 g
TFP2000-G1 -827-05	5000 mm	273.00 g
TFP2000-G1 -830-05	5000 mm	273.00 g
TFP2000-G1 -840-05	5000 mm	273.00 g
TFP2000-G1 -865-05	5000 mm	273.00 g
TFP2000-G1 -850-05	5000 mm	273.00 g

Temperatures & operating conditions

Product description	Temperature range in operation at Tc point	Temperature range at storage
TFP300-G1 -827-05	-25...80 °C	-30...85 °C
TFP300-G1 -830-05	-25...80 °C	-30...85 °C
TFP300-G1 -840-05	-25...80 °C	-30...85 °C
TFP300-G1 -865-05	-25...80 °C	-30...85 °C
TFP300-G1 -850-05	-25...80 °C	-30...85 °C
TFP1000-G1 -827-05	-25...80 °C	-30...85 °C
TFP1000-G1 -830-05	-25...80 °C	-30...85 °C
TFP1000-G1 -840-05	-25...80 °C	-30...85 °C
TFP1000-G1 -865-05	-25...80 °C	-30...85 °C
TFP1000-G1 -850-05	-25...80 °C	-30...85 °C
TFP2000-G1 -827-05	-25...80 °C	-30...85 °C
TFP2000-G1 -830-05	-25...80 °C	-30...85 °C
TFP2000-G1 -840-05	-25...80 °C	-30...85 °C
TFP2000-G1 -865-05	-25...80 °C	-30...85 °C
TFP2000-G1 -850-05	-25...80 °C	-30...85 °C

Product family datasheet

Additional product data

Product description	Predecessor EAN	ID of contained light source
TFP300-G1 -827-05	4052899528031, 4052899528116	LS_SHZ_600315
TFP300-G1 -830-05	4052899528055, 4052899528130	LS_SHZ_600316
TFP300-G1 -840-05	4052899528079, 4052899528154	LS_SHZ_600317
TFP300-G1 -865-05	4052899528093, 4052899528178	LS_SHZ_600319
TFP300-G1 -850-05		LS_SHZ_600318
TFP1000-G1 -827-05	4052899526211	LS_SHZ_600320
TFP1000-G1 -830-05	4052899526235	LS_SHZ_600321
TFP1000-G1 -840-05	4052899526259	LS_SHZ_600322
TFP1000-G1 -865-05	4052899526273	LS_SHZ_600324
TFP1000-G1 -850-05		LS_SHZ_600323
TFP2000-G1 -827-05	4052899528468	LS_SHZ_600298
TFP2000-G1 -830-05	4052899528482	LS_SHZ_600326
TFP2000-G1 -840-05	4052899528505	LS_SHZ_600327
TFP2000-G1 -865-05	4052899528529	LS_SHZ_600329
TFP2000-G1 -850-05		LS_SHZ_600328

Certificates & standards

Product description	Standards	Energy efficiency class of the contained light source
TFP300-G1 -827-05	CE/ENEC/EAC	E
TFP300-G1 -830-05	CE/ENEC/EAC	E
TFP300-G1 -840-05	CE/ENEC/EAC	E
TFP300-G1 -865-05	CE/ENEC/EAC	E
TFP300-G1 -850-05	CE/ENEC/EAC	E
TFP1000-G1 -827-05	CE/ENEC/EAC	F
TFP1000-G1 -830-05	CE/ENEC/EAC	E
TFP1000-G1 -840-05	CE/ENEC/EAC	E
TFP1000-G1 -865-05	CE/ENEC/EAC	E
TFP1000-G1 -850-05	CE/ENEC/EAC	E
TFP2000-G1 -827-05	CE/ENEC/EAC	F
TFP2000-G1 -830-05	CE/ENEC/EAC	E
TFP2000-G1 -840-05	CE/ENEC/EAC	E
TFP2000-G1 -865-05	CE/ENEC/EAC	E
TFP2000-G1 -850-05	CE/ENEC/EAC	E

Logistical data

Product description	Commodity code
TFP300-G1 -827-05	85395100000
TFP300-G1 -830-05	85395100000
TFP300-G1 -840-05	85395100000
TFP300-G1 -865-05	85395100000
TFP300-G1 -850-05	85395100000
TFP1000-G1 -827-05	85395100000
TFP1000-G1 -830-05	85395100000
TFP1000-G1 -840-05	85395100000
TFP1000-G1 -865-05	85395100000
TFP1000-G1 -850-05	85395100000
TFP2000-G1 -827-05	85395100000
TFP2000-G1 -830-05	85395100000
TFP2000-G1 -840-05	85395100000
TFP2000-G1 -865-05	85395100000
TFP2000-G1 -850-05	85395100000

Environmental information
Information according Art. 33 of EU Regulation (EC) 1907/2006 (REACH)

Product description	Date of Declaration	Primary Article Identifier	Candidate List Substance 1
TFP300-G1 -827-05	07-07-2023	4062172106627	Lead
TFP300-G1 -830-05	07-07-2023	4062172106641	Lead
TFP300-G1 -840-05	11-04-2023	4062172106665	No declarable substances contained
TFP300-G1 -865-05	11-04-2023	4062172106702	No declarable substances contained
TFP300-G1 -850-05	11-04-2023	4062172106689	No declarable substances contained
TFP1000-G1 -827-05	07-07-2023	4062172106726	Lead
TFP1000-G1 -830-05	07-07-2023	4062172106740	Lead
TFP1000-G1 -840-05	07-07-2023	4062172106764	Lead
TFP1000-G1 -865-05	07-07-2023	4062172106801	Lead
TFP1000-G1 -850-05	21-07-2023	4062172106788	Lead
TFP2000-G1 -827-05	07-07-2023	4062172106825	Lead
TFP2000-G1 -830-05	07-07-2023	4062172106849	Lead
TFP2000-G1 -840-05	07-07-2023	4062172106863	Lead
TFP2000-G1 -865-05	07-07-2023	4062172106900	Lead
TFP2000-G1 -850-05	07-07-2023	4062172106887	Lead
Product description	CAS No. of substance 1	Safe Use Instruction	Declaration No. in SCIP database
TFP300-G1 -827-05	7439-92-1	The identification of the Candidate List substance is sufficient to allow safe use of the article.	aa00d901-7681-43d3-b39a-799982271c08

Product family datasheet

Product description	CAS No. of substance 1	Safe Use Instruction	Declaration No. in SCIP database
TFP300-G1 -830-05	7439-92-1	The identification of the Candidate List substance is sufficient to allow safe use of the article.	01dbb983-4301-49d5-a5f5-39360f03e065
TFP300-G1 -840-05			No declarable substances contained
TFP300-G1 -865-05			No declarable substances contained
TFP300-G1 -850-05			No declarable substances contained
TFP1000-G1 -827-05	7439-92-1	The identification of the Candidate List substance is sufficient to allow safe use of the article.	807d90b4-f529-4a4c-8d2b-9714849306c4
TFP1000-G1 -830-05	7439-92-1	The identification of the Candidate List substance is sufficient to allow safe use of the article.	dd03dde0-7181-412a-a79f-c57297169c50
TFP1000-G1 -840-05	7439-92-1	The identification of the Candidate List substance is sufficient to allow safe use of the article.	59209483-c933-420b-847f-5325be7af197
TFP1000-G1 -865-05	7439-92-1	The identification of the Candidate List substance is sufficient to allow safe use of the article.	e037d093-3865-48e6-919d-0f13fc36131f
TFP1000-G1 -850-05	7439-92-1	The identification of the Candidate List substance is sufficient to allow safe use of the article.	e3a453a2-4f36-4c4f-aa72-374a3c937902
TFP2000-G1 -827-05	7439-92-1	The identification of the Candidate List substance is sufficient to allow safe use of the article.	ae550d68-6088-4f32-b3a4-eba43f638b02
TFP2000-G1 -830-05	7439-92-1	The identification of the Candidate List substance is sufficient to allow safe use of the article.	ab29cb42-27c3-4c7b-9860-a11730119d8c
TFP2000-G1 -840-05	7439-92-1	The identification of the Candidate List substance is sufficient to allow safe use of the article.	b74546d0-fb3b-42f4-8aa8-2cf3bd0b0656
TFP2000-G1 -865-05	7439-92-1	The identification of the Candidate List substance is sufficient to allow safe use of the article.	b61971db-48c3-417d-98aa-cc744c4926f9
TFP2000-G1 -850-05	7439-92-1	The identification of the Candidate List substance is sufficient to allow safe use of the article.	0cb3a442-2d96-4be1-a748-7080ad858a93

Product family datasheet

Equipment / Accessories

- Simplified connection with optional matching CONNECTsystem
- Flexessories: a complete set of aluminum channels with diffusers and lenses
- Drivers and dimmers: wide selection of OPTOTRONIC 24 V DALI, DMX and BLE

Application advice

For more detailed application information and graphics please see product datasheet.

Sales and Technical Support

Sales and Technical Support www.osram.com

Download Data

File	
	User instruction TEC Flex IP66
	Product Datasheet TEC Flex IP66 Product Datasheet (EN)
	Brochures Light is strong - Discover the versatile and flexible lighting system OSRAM 24V TEC Flex (EN)
	Certificates TFX ENEC 130520
	Declarations of conformity TECFlex CE 4210017 080823
	CAD data DWG TEC Flex and TEC Flex Shortpitch
	Eulumdat EULUMDAT TEC Flex Protect
	Eulumdat TFP300-G1-827 LTD 130122
	IES data TFP300-G1-827 IES 130122
	Eulumdat TFP300-G1-830 LTD 130122
	IES data TFP300-G1-830 IES 130122
	Eulumdat TFP300-G1-840 LTD 130122
	IES data TFP300-G1-840 IES 130122

Product family datasheet

	Eulumdat TFP300-G1-865 LTD 130122
	IES data TFP300-G1-865 IES 130122
	Eulumdat TFP300-G1-850 LTD 130122
	IES data TFP300-G1-850 IES 130122
	Eulumdat TFP1000-G1-827 LTD 130122
	IES data TFP1000-G1-827 IES 130122
	Eulumdat TFP1000-G1-830 LTD 130122
	IES data TFP1000-G1-830 IES 130122
	Eulumdat TFP1000-G1-840 LTD 130122
	IES data TFP1000-G1-840 IES 130122
	Eulumdat TFP1000-G1-865 LTD 130122
	IES data TFP1000-G1-865 IES 130122
	Eulumdat TFP1000-G1-850 LTD 130122
	IES data TFP1000-G1-850 IES 130122
	Eulumdat TFP2000-G1-827 LTD 130122
	IES data TFP2000-G1-827 IES 130122
	Eulumdat TFP2000-G1-830 LTD 130122
	IES data TFP2000-G1-830 IES 130122
	Eulumdat TFP2000-G1-840 LTD 130122
	IES data TFP2000-G1-840 IES 130122
	Eulumdat TFP2000-G1-865 LTD 130122
	IES data TFP2000-G1-865 IES 130122
	Eulumdat TFP2000-G1-850 LTD 130122

	IES data TFP2000-G1-850 IES 130122
---	---------------------------------------

Ecodesign regulation information:

- This product is considered to be a "containing product" in the sense of Regulations (EU) 2019/2020 and (EU) 2019/2015.
- Tolerances of the reported values, are according to LED Modules Performance standard IEC/EN 62717.
- In general, the replacement of the contained light sources without permanent damage to the product with the use of common available tools is possible in the final application when they can be dismantled from the installation environment and substituted for the necessary number of light sources restoring its full electrical/mechanical/thermal/optical functionality by means of a professional installer. In the contrary, and limited to the LINEARlight Flex Diffuse, LINEARlight Rigid Finesse, GINO LED Flex Diffuse and LUMINENT Milky product families, the contained light source is an integrated part of the containing product and its removal can only be done by causing a permanent damage to the containing product due to its tight mechanical, electrical, optical, thermal interaction and/or environmental protection with or from the containing product. Therefore, a replacement of the light source with the use of common available tools is not justified.
- Dismantling of light sources from containing products at end of life: Containing products with light sources which are scalable in length can be cut to the length of the contained light source and if applicable mechanically detached from protective and/or optical covers. Containing products shall be separated from building material and/or from other additional mounting accessories by means of a professional installer. Separate control gear and light sources must be disposed of at certified disposal companies in accordance with Directive 2012/19/EU (WEEE) in the EU and with Waste Electrical and Electronic Equipment (WEEE) Regulations 2013 in the UK. For this purpose, collection points for recycling centres and take-back systems (CRSO) are available from retailers or private disposal companies, which accept separate control gear and light sources free of charge. In this way, raw materials are conserved and materials are recycled.

Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4062172106627	TFP300-G1 -827-05	Shipping carton box 10	280 mm x 305 mm x 180 mm	15.37 dm ³	3664.00 g
4062172106641	TFP300-G1 -830-05	Shipping carton box 10	280 mm x 305 mm x 180 mm	15.37 dm ³	3664.00 g
4062172106665	TFP300-G1 -840-05	Shipping carton box 10	280 mm x 305 mm x 180 mm	15.37 dm ³	3664.00 g
4062172106702	TFP300-G1 -865-05	Shipping carton box 10	280 mm x 305 mm x 180 mm	15.37 dm ³	3664.00 g
4062172106689	TFP300-G1 -850-05	Shipping carton box 10	280 mm x 305 mm x 180 mm	15.37 dm ³	3664.00 g
4062172106726	TFP1000-G1 -827-05	Shipping carton box 10	280 mm x 305 mm x 180 mm	15.37 dm ³	3664.00 g
4062172106740	TFP1000-G1 -830-05	Shipping carton box 10	280 mm x 305 mm x 180 mm	15.37 dm ³	3664.00 g
4062172106764	TFP1000-G1 -840-05	Shipping carton box 10	280 mm x 305 mm x 180 mm	15.37 dm ³	3664.00 g
4062172106801	TFP1000-G1 -865-05	Shipping carton box 10	280 mm x 305 mm x 180 mm	15.37 dm ³	3664.00 g

Product family datasheet

Logistical Data

4062172106788	TFP1000-G1 -850-05	Shipping carton box 10	280 mm x 305 mm x 180 mm	15.37 dm ³	3664.00 g
4062172106825	TFP2000-G1 -827-05	Shipping carton box 10	280 mm x 305 mm x 180 mm	15.37 dm ³	3704.00 g
4062172106849	TFP2000-G1 -830-05	Shipping carton box 10	280 mm x 305 mm x 180 mm	15.37 dm ³	3704.00 g
4062172106863	TFP2000-G1 -840-05	Shipping carton box 10	280 mm x 305 mm x 180 mm	15.37 dm ³	3704.00 g
4062172106900	TFP2000-G1 -865-05	Shipping carton box 10	280 mm x 305 mm x 180 mm	15.37 dm ³	3704.00 g
4062172106887	TFP2000-G1 -850-05	Shipping carton box 10	280 mm x 305 mm x 180 mm	15.37 dm ³	3704.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

Accessories Optional

Product description	Accessory name	Accessory code
TFP300-G1 -827-05	ENDCAP -IP67 KIT 10PCS	▶ 4062172176552
TFP300-G1 -827-05	LTS-SLIMTRACK -2000 KIT 5 PCS	▶ 4062172207300
TFP300-G1 -827-05	FX-QMS-G1 -TU15H6-300	▶ 4052899448865
TFP300-G1 -827-05	FX-QMS-G1 -TU15H6W3-300	▶ 4052899448889
TFP300-G1 -827-05	FX-QMS-G1 -TU16H12W3-300	▶ 4052899448988
TFP300-G1 -827-05	FX-QMS-G1 -TU16H12-300	▶ 4052899448964
TFP300-G1 -827-05	FX -SC08-G2-CT4PJ	▶ 4052899464858
TFP300-G1 -827-05	FX -SC08-G2-C2PF-IP54-0500	▶ 4052899464889
TFP300-G1 -827-05	FX -SC08-G2--BTJ-IP54	▶ 4052899568853
TFP300-G1 -827-05	FX-QMS-G1 -TU16H12LS-300	▶ 4052899449046
TFP300-G1 -830-05	ENDCAP -IP67 KIT 10PCS	▶ 4062172176552
TFP300-G1 -830-05	LTS-SLIMTRACK -2000 KIT 5 PCS	▶ 4062172207300
TFP300-G1 -830-05	FX-QMS-G1 -TU15H6-300	▶ 4052899448865
TFP300-G1 -830-05	FX-QMS-G1 -TU15H6W3-300	▶ 4052899448889
TFP300-G1 -830-05	FX-QMS-G1 -TU16H12W3-300	▶ 4052899448988
TFP300-G1 -830-05	FX-QMS-G1 -TU16H12-300	▶ 4052899448964
TFP300-G1 -830-05	FX -SC08-G2-CT4PJ	▶ 4052899464858
TFP300-G1 -830-05	FX -SC08-G2-C2PF-IP54-0500	▶ 4052899464889
TFP300-G1 -830-05	FX -SC08-G2--BTJ-IP54	▶ 4052899568853
TFP300-G1 -830-05	FX-QMS-G1 -TU16H12LS-300	▶ 4052899449046

Product family datasheet

TFP300-G1 -840-05	ENDCAP -IP67 KIT 10PCS	▶ 4062172176552
TFP300-G1 -840-05	LTS-SLIMTRACK -2000 KIT 5 PCS	▶ 4062172207300
TFP300-G1 -840-05	FX-QMS-G1 -TU15H6-300	▶ 4052899448865
TFP300-G1 -840-05	FX-QMS-G1 -TU15H6W3-300	▶ 4052899448889
TFP300-G1 -840-05	FX-QMS-G1 -TU16H12W3-300	▶ 4052899448988
TFP300-G1 -840-05	FX-QMS-G1 -TU16H12-300	▶ 4052899448964
TFP300-G1 -840-05	FX -SC08-G2-CT4PJ	▶ 4052899464858
TFP300-G1 -840-05	FX -SC08-G2-C2PF-IP54-0500	▶ 4052899464889
TFP300-G1 -840-05	FX -SC08-G2--BTJ-IP54	▶ 4052899568853
TFP300-G1 -840-05	FX-QMS-G1 -TU16H12LS-300	▶ 4052899449046
TFP300-G1 -865-05	ENDCAP -IP67 KIT 10PCS	▶ 4062172176552
TFP300-G1 -865-05	LTS-SLIMTRACK -2000 KIT 5 PCS	▶ 4062172207300
TFP300-G1 -865-05	FX-QMS-G1 -TU15H6-300	▶ 4052899448865
TFP300-G1 -865-05	FX-QMS-G1 -TU15H6W3-300	▶ 4052899448889
TFP300-G1 -865-05	FX-QMS-G1 -TU16H12W3-300	▶ 4052899448988
TFP300-G1 -865-05	FX-QMS-G1 -TU16H12-300	▶ 4052899448964
TFP300-G1 -865-05	FX -SC08-G2-CT4PJ	▶ 4052899464858
TFP300-G1 -865-05	FX -SC08-G2-C2PF-IP54-0500	▶ 4052899464889
TFP300-G1 -865-05	FX -SC08-G2--BTJ-IP54	▶ 4052899568853
TFP300-G1 -865-05	FX-QMS-G1 -TU16H12LS-300	▶ 4052899449046
TFP300-G1 -850-05	ENDCAP -IP67 KIT 10PCS	▶ 4062172176552
TFP300-G1 -850-05	LTS-SLIMTRACK -2000 KIT 5 PCS	▶ 4062172207300
TFP300-G1 -850-05	FX-QMS-G1 -TU15H6-300	▶ 4052899448865
TFP300-G1 -850-05	FX-QMS-G1 -TU15H6W3-300	▶ 4052899448889
TFP300-G1 -850-05	FX-QMS-G1 -TU16H12W3-300	▶ 4052899448988
TFP300-G1 -850-05	FX-QMS-G1 -TU16H12-300	▶ 4052899448964
TFP300-G1 -850-05	FX -SC08-G2-CT4PJ	▶ 4052899464858
TFP300-G1 -850-05	FX -SC08-G2-C2PF-IP54-0500	▶ 4052899464889
TFP300-G1 -850-05	FX -SC08-G2--BTJ-IP54	▶ 4052899568853
TFP300-G1 -850-05	FX-QMS-G1 -TU16H12LS-300	▶ 4052899449046
TFP1000-G1 -827-05	ENDCAP -IP67 KIT 10PCS	▶ 4062172176552
TFP1000-G1 -827-05	LTS-SLIMTRACK -2000 KIT 5 PCS	▶ 4062172207300
TFP1000-G1 -827-05	FX-QMS-G1 -TU15H6-300	▶ 4052899448865
TFP1000-G1 -827-05	FX-QMS-G1 -TU15H6W3-300	▶ 4052899448889
TFP1000-G1 -827-05	FX-QMS-G1 -TU16H12W3-300	▶ 4052899448988
TFP1000-G1 -827-05	FX-QMS-G1 -TU16H12-300	▶ 4052899448964
TFP1000-G1 -827-05	FX -SC08-G2-CT4PJ	▶ 4052899464858
TFP1000-G1 -827-05	FX -SC08-G2-C2PF-IP54-0500	▶ 4052899464889

Product family datasheet

TFP1000-G1 -827-05	FX -SC08-G2--BTJ-IP54	▶ 4052899568853
TFP1000-G1 -827-05	FX-QMS-G1 -TU16H12LS-300	▶ 4052899449046
TFP1000-G1 -830-05	ENDCAP -IP67 KIT 10PCS	▶ 4062172176552
TFP1000-G1 -830-05	LTS-SLIMTRACK -2000 KIT 5 PCS	▶ 4062172207300
TFP1000-G1 -830-05	FX-QMS-G1 -TU15H6-300	▶ 4052899448865
TFP1000-G1 -830-05	FX-QMS-G1 -TU15H6W3-300	▶ 4052899448889
TFP1000-G1 -830-05	FX-QMS-G1 -TU16H12W3-300	▶ 4052899448988
TFP1000-G1 -830-05	FX-QMS-G1 -TU16H12-300	▶ 4052899448964
TFP1000-G1 -830-05	FX -SC08-G2-CT4PJ	▶ 4052899464858
TFP1000-G1 -830-05	FX -SC08-G2-C2PF-IP54-0500	▶ 4052899464889
TFP1000-G1 -830-05	FX -SC08-G2--BTJ-IP54	▶ 4052899568853
TFP1000-G1 -830-05	FX-QMS-G1 -TU16H12LS-300	▶ 4052899449046
TFP1000-G1 -840-05	ENDCAP -IP67 KIT 10PCS	▶ 4062172176552
TFP1000-G1 -840-05	LTS-SLIMTRACK -2000 KIT 5 PCS	▶ 4062172207300
TFP1000-G1 -840-05	FX-QMS-G1 -TU15H6-300	▶ 4052899448865
TFP1000-G1 -840-05	FX-QMS-G1 -TU15H6W3-300	▶ 4052899448889
TFP1000-G1 -840-05	FX-QMS-G1 -TU16H12W3-300	▶ 4052899448988
TFP1000-G1 -840-05	FX-QMS-G1 -TU16H12-300	▶ 4052899448964
TFP1000-G1 -840-05	FX -SC08-G2-CT4PJ	▶ 4052899464858
TFP1000-G1 -840-05	FX -SC08-G2-C2PF-IP54-0500	▶ 4052899464889
TFP1000-G1 -840-05	FX -SC08-G2--BTJ-IP54	▶ 4052899568853
TFP1000-G1 -840-05	FX-QMS-G1 -TU16H12LS-300	▶ 4052899449046
TFP1000-G1 -865-05	ENDCAP -IP67 KIT 10PCS	▶ 4062172176552
TFP1000-G1 -865-05	LTS-SLIMTRACK -2000 KIT 5 PCS	▶ 4062172207300
TFP1000-G1 -865-05	FX-QMS-G1 -TU15H6-300	▶ 4052899448865
TFP1000-G1 -865-05	FX-QMS-G1 -TU15H6W3-300	▶ 4052899448889
TFP1000-G1 -865-05	FX-QMS-G1 -TU16H12W3-300	▶ 4052899448988
TFP1000-G1 -865-05	FX-QMS-G1 -TU16H12-300	▶ 4052899448964
TFP1000-G1 -865-05	FX -SC08-G2-CT4PJ	▶ 4052899464858
TFP1000-G1 -865-05	FX -SC08-G2-C2PF-IP54-0500	▶ 4052899464889
TFP1000-G1 -865-05	FX -SC08-G2--BTJ-IP54	▶ 4052899568853
TFP1000-G1 -865-05	FX-QMS-G1 -TU16H12LS-300	▶ 4052899449046
TFP1000-G1 -850-05	ENDCAP -IP67 KIT 10PCS	▶ 4062172176552
TFP1000-G1 -850-05	LTS-SLIMTRACK -2000 KIT 5 PCS	▶ 4062172207300
TFP1000-G1 -850-05	FX-QMS-G1 -TU15H6-300	▶ 4052899448865
TFP1000-G1 -850-05	FX-QMS-G1 -TU15H6W3-300	▶ 4052899448889
TFP1000-G1 -850-05	FX-QMS-G1 -TU16H12W3-300	▶ 4052899448988
TFP1000-G1 -850-05	FX-QMS-G1 -TU16H12-300	▶ 4052899448964

Product family datasheet

TFP1000-G1 -850-05	FX -SC08-G2-CT4PJ	▶ 4052899464858
TFP1000-G1 -850-05	FX -SC08-G2-C2PF-IP54-0500	▶ 4052899464889
TFP1000-G1 -850-05	FX -SC08-G2--BTJ-IP54	▶ 4052899568853
TFP1000-G1 -850-05	FX-QMS-G1 -TU16H12LS-300	▶ 4052899449046
TFP2000-G1 -827-05	ENDCAP -IP67 KIT 10PCS	▶ 4062172176552
TFP2000-G1 -827-05	LTS-SLIMTRACK -2000 KIT 5 PCS	▶ 4062172207300
TFP2000-G1 -827-05	FX-QMS-G1 -TU15H6-300	▶ 4052899448865
TFP2000-G1 -827-05	FX-QMS-G1 -TU15H6W3-300	▶ 4052899448889
TFP2000-G1 -827-05	FX-QMS-G1 -TU16H12W3-300	▶ 4052899448988
TFP2000-G1 -827-05	FX-QMS-G1 -TU16H12-300	▶ 4052899448964
TFP2000-G1 -827-05	FX -SC08-G2-CT4PJ	▶ 4052899464858
TFP2000-G1 -827-05	FX -SC08-G2-C2PF-IP54-0500	▶ 4052899464889
TFP2000-G1 -827-05	FX -SC08-G2--BTJ-IP54	▶ 4052899568853
TFP2000-G1 -827-05	FX-QMS-G1 -TU16H12LS-300	▶ 4052899449046
TFP2000-G1 -830-05	ENDCAP -IP67 KIT 10PCS	▶ 4062172176552
TFP2000-G1 -830-05	LTS-SLIMTRACK -2000 KIT 5 PCS	▶ 4062172207300
TFP2000-G1 -830-05	FX-QMS-G1 -TU15H6-300	▶ 4052899448865
TFP2000-G1 -830-05	FX-QMS-G1 -TU15H6W3-300	▶ 4052899448889
TFP2000-G1 -830-05	FX-QMS-G1 -TU16H12W3-300	▶ 4052899448988
TFP2000-G1 -830-05	FX-QMS-G1 -TU16H12-300	▶ 4052899448964
TFP2000-G1 -830-05	FX -SC08-G2-CT4PJ	▶ 4052899464858
TFP2000-G1 -830-05	FX -SC08-G2-C2PF-IP54-0500	▶ 4052899464889
TFP2000-G1 -830-05	FX -SC08-G2--BTJ-IP54	▶ 4052899568853
TFP2000-G1 -830-05	FX-QMS-G1 -TU16H12LS-300	▶ 4052899449046
TFP2000-G1 -840-05	ENDCAP -IP67 KIT 10PCS	▶ 4062172176552
TFP2000-G1 -840-05	LTS-SLIMTRACK -2000 KIT 5 PCS	▶ 4062172207300
TFP2000-G1 -840-05	FX-QMS-G1 -TU15H6-300	▶ 4052899448865
TFP2000-G1 -840-05	FX-QMS-G1 -TU15H6W3-300	▶ 4052899448889
TFP2000-G1 -840-05	FX-QMS-G1 -TU16H12W3-300	▶ 4052899448988
TFP2000-G1 -840-05	FX-QMS-G1 -TU16H12-300	▶ 4052899448964
TFP2000-G1 -840-05	FX -SC08-G2-CT4PJ	▶ 4052899464858
TFP2000-G1 -840-05	FX -SC08-G2-C2PF-IP54-0500	▶ 4052899464889
TFP2000-G1 -840-05	FX -SC08-G2--BTJ-IP54	▶ 4052899568853
TFP2000-G1 -840-05	FX-QMS-G1 -TU16H12LS-300	▶ 4052899449046
TFP2000-G1 -865-05	ENDCAP -IP67 KIT 10PCS	▶ 4062172176552
TFP2000-G1 -865-05	LTS-SLIMTRACK -2000 KIT 5 PCS	▶ 4062172207300
TFP2000-G1 -865-05	FX-QMS-G1 -TU15H6-300	▶ 4052899448865
TFP2000-G1 -865-05	FX-QMS-G1 -TU15H6W3-300	▶ 4052899448889

Product family datasheet

TFP2000-G1 -865-05	FX-QMS-G1 -TU16H12W3-300	▶ 4052899448988
TFP2000-G1 -865-05	FX-QMS-G1 -TU16H12-300	▶ 4052899448964
TFP2000-G1 -865-05	FX -SC08-G2-CT4PJ	▶ 4052899464858
TFP2000-G1 -865-05	FX -SC08-G2-C2PF-IP54-0500	▶ 4052899464889
TFP2000-G1 -865-05	FX -SC08-G2--BTJ-IP54	▶ 4052899568853
TFP2000-G1 -865-05	FX-QMS-G1 -TU16H12LS-300	▶ 4052899449046
TFP2000-G1 -850-05	ENDCAP -IP67 KIT 10PCS	▶ 4062172176552
TFP2000-G1 -850-05	LTS-SLIMTRACK -2000 KIT 5 PCS	▶ 4062172207300
TFP2000-G1 -850-05	FX-QMS-G1 -TU15H6-300	▶ 4052899448865
TFP2000-G1 -850-05	FX-QMS-G1 -TU15H6W3-300	▶ 4052899448889
TFP2000-G1 -850-05	FX-QMS-G1 -TU16H12W3-300	▶ 4052899448988
TFP2000-G1 -850-05	FX-QMS-G1 -TU16H12-300	▶ 4052899448964
TFP2000-G1 -850-05	FX -SC08-G2-CT4PJ	▶ 4052899464858
TFP2000-G1 -850-05	FX -SC08-G2-C2PF-IP54-0500	▶ 4052899464889
TFP2000-G1 -850-05	FX -SC08-G2--BTJ-IP54	▶ 4052899568853
TFP2000-G1 -850-05	FX-QMS-G1 -TU16H12LS-300	▶ 4052899449046

Disclaimer

— Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.